

Specifications for IP Printer - 600 dpi - 240 V

Application	Asset Identification; Barcode Labelling; Wire & Cable Marking; Circuit Board Identification
Article No.	360847
Colour Capability	Monocolour
Continuous vs Die Cut Labels	Continuous Tape & Die Cut Labels
Keyboard Type	None
Description	Brady's IP™ Thermal Transfer Printer is a new, smart solution for high-performance printing. The Brady IP™ Printer is a fully integrated, easy-to-use printer, material, and software system. Smart Cell technology allows the printer, materials, and ribbon to communicate with each other. The system offers material recognition, automatic formatting, and user-friendly printer features for labels, sleeves, and tags. Brady IP™ Printer detects loaded material and ribbon and displays the user information on the LCD. The material information is sent to the software, where template and settings are automatically populated. Create data on template, then click and print. Load, click, and print. It's just that simple.
Order Reference	BP-THT-IP600-UK
PC Connectivity	Yes
Portability	No
Print Speed (mm/sec)	200
Print Technology	Thermal Transfer
Size - Depth (mm)	435.00
Size - Height (mm)	312.00
Size - Width (mm)	240.00
Smart Cell	Yes
Additional Information	8 hours of operation per day for 5 days
Stand Alone Printing	With USB Master
Total Qty per Pack	1 Piece(s) / Piece
Weight (kg)	5.9
Max. Label Width (mm)	105.66
Max. Liner Width	106.68

(mm)	
Max. Print Length (mm)	508.00
Max. Print Width (mm)	105.66
Minimum Label Height (mm)	3.20
Multi-Line Print	Yes
Minimum Label Width (mm)	6.40
Min. Label Length (mm)	3.17
Min. Liner Width (mm)	25.40