



6348260-3

**Fiber Optic Patch Cord, singlemode, SC/PC-SC/PC, duplex, 2.5 mm tight cable, LSZH, 3 m, yellow**

## Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber patch cord, duplex
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Body Features

Boot Color (End A)	Red/Black
Boot Color (End B)	Red/Black
Boot Type (End A)	Short
Boot Type (End B)	Short
Connector Color (End A)	Blue
Connector Color (End B)	Blue

## Configuration Features

Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

## Construction Materials

Jacket Color	Yellow
Total Fibers, quantity	2

## Dimensions

Assembly Length	3.00 m   9.84 ft
Cable Outer Diameter	.118 in   3 mm

## General Specifications

Interface, connector A	SC
Interface, connector B	SC
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard

## Industry Standards

Flammability Rating	LSZH
---------------------	------

6348260-3

## Product Type Features

---

Fiber Type	OS1
Fiber Diameter	9/125 $\mu\text{m}$
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Fiber Cable Type	Duplex, dualzip
Optical Mode	Singlemode

## Signal Characteristics

---

Insertion Loss, maximum (End A)	0.30 dB
Insertion Loss, maximum (End B)	0.30 dB
Return Loss, minimum	45 dB

## Regulatory Compliance/Certifications

---

Agency	Classification
RoHS 2011/65/EU	Compliant

### \* Footnotes

---

Assembly Length	Assembly length includes the breakout lengths
-----------------	---