


SIVACON, Roof, Closed, IP55, W: 600 mm, T: 500 mm, zinc-plated



| Model                               |             |                   |
|-------------------------------------|-------------|-------------------|
| product brand name                  | SIVACON     |                   |
| product designation                 | top plate   |                   |
| design of the product               | Closed      |                   |
| design of the surface               | zinc plated |                   |
| design of the product EMC version   | No          |                   |
| Protection class                    |             |                   |
| protection class IP                 | IP55        |                   |
| Suitability                         |             |                   |
| suitability for use for outside use | No          |                   |
| Product details                     |             |                   |
| product component                   |             |                   |
| • cable entry                       |             |                   |
| • ventilation                       |             |                   |
| Mechanical Design                   |             |                   |
| width                               | 600 mm      |                   |
| depth                               | 500 mm      |                   |
| material                            | steel       |                   |
| Approvals Certificates              |             |                   |
| General Product Approval            |             | Test Certificates |
|                                     |             | other             |



[Special Test Certificate](#)

[Confirmation](#)

[Miscellaneous](#)

|                               |                                             |
|-------------------------------|---------------------------------------------|
| other                         | Environment                                 |
| <a href="#">Miscellaneous</a> | <a href="#">Environmental Confirmations</a> |
|                               |                                             |

| Further information                                                                                                                                                                                                           |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Information on the packaging<br><a href="https://support.industry.siemens.com/cs/ww/en/view/109813875">https://support.industry.siemens.com/cs/ww/en/view/109813875</a>                                                       |
| Information- and Downloadcenter (Catalogs, Brochures,...)<br><a href="http://www.siemens.com/lowvoltage/catalogs">http://www.siemens.com/lowvoltage/catalogs</a>                                                              |
| Industry Mall (Online ordering system)<br><a href="https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1065-2UD11-0A">https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1065-2UD11-0A</a> |
| Service&Support (Manuals, Certificates, Characteristics, FAQs,...)                                                                                                                                                            |

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1065-2UD11-0A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF1065-2UD11-0A](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1065-2UD11-0A)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

7/24/2023 

