

611.10.063 0 mbar...40 mbar 1/4 NPT lower mount

Capsule pressure gauge, standard series

Item number: 38408495

Quantity: 1 pcs.

Order code: 611.10-C-MAEOZZ-NB-UZZAZZZ-ZZZ V3ABZZ2CBKAMC
DIAL-IAZ1ZZZZZZ1Z- ZZZZ4ZZZZ
LABEL-ASASZDE-

Overview: 611.10.063 0 mbar...40 mbar 1/4 NPT lower mount
Capsule pressure gauge, standard series
acrylic (PMMA)
class 1.6
Movement: copper alloy
Single packing
Case: black steel
WIKA
Cl.1.6
inner packages label: Standard (with Wika Logo) outside packages label: Standard (with Wika Logo)

Details: Capsule pressure gauge, standard series
Model: 611.10
Specifications according to data sheet: PM 06.01
Accuracy class: class 1.6
Measuring system: copper alloy
Nominal size: 063 mm
Unit: mbar
Scale range: 0 mbar...40 mbar
Process connection: 1/4 NPT
Connector location: lower mount
Window: acrylic (PMMA)
Case type: without blow-out disc on top
Accuracy class: class 1.6
Movement: copper alloy
Ingress protection: IP 32
Package: Single packing
Case: black steel
Case colour: black
Pointer colour: black
Dial description:
Pressure Gauge Standard: International (standard Europe)
color for 1.scale (outside): black
dial background: White
Manufacturer logo: *WIKA*
accuracy class on dial: *Cl.1.6*

Date: 11/06/2026



inner packages label: Standard (with Wika Logo)

outside packages label: Standard (with Wika Logo)