

Technical data

Material	: Polyvinylchloride (hard PVC)
Colour	: grey RAL 7030
Operating temperature	: -5 °C to +65 °C

	Typical values	Test method
Density	: 1.55 g/cm ³	DIN 53479
Flammability	: self-extinguishing V0	UL 94
Formaldehyde	: not included	
Cadmium	: not included	
Dielectric conductivity	: 3.2 - 4.0	AST D150
Dielectric strength	: 70 kV/mm	IEC 243
Resistance	: 10 ¹³ Ohm	IEC 93
Specification	: UL	

HellermannTyton

 HellermannTyton GmbH
 Grosser Moorweg 45
 D-25436 Tornesch

 Telefon: +49 (0) 4122/701-1
 Telefax: +49 (0) 4122/701-400

This information is based on our experience and does not imply suitability without prior testing. Due to the variables of manufacture and environmental conditions it is strongly recommended that samples are tested in-situ.