



182.72.104.66NUTRStützrollen

Yoke type track rollers NUTR45100 (Series NUTR)

full complement cylindrical roller set, with axial guidance,
labyrinth seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	45 mm
D	100 mm
B	32 mm
C	30 mm
d ₂	55,2 mm
r ₁ min	0,6 mm
r _{min}	1,1 mm
m	1396 g Mass
C _r w	72000 N Effective dynamic load rating as track roller (radial)
C _{0r} w	115000 N Effective static load rating as track roller (radial)
F _r per	106000 N Permissible dynamic radial load
F _{0r} per	115000 N Permissible static radial load
C _{ur} w	15800 N Fatigue limit load
n _D G	1400 1/min Speed (with continuous operation and grease lubrication)

