



40VMax Rear-handle Chainsaw XGT®

UC030G

40VMax, 0 - 29.0 m/s

Model UC030G is a 400 / 450 / 500 mm rear handle chain saw powered by a 40VMax XGT Li-Ion battery.

In combination with the new high capacity battery BL4080H this machine offers work efficiency equal or superior to that of a 50cc-class engine chain saw, enabling smooth felling of trees approx. 400 mm in diameter. Saw chain type 85TXL / 22BPX



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Chain Speed (No Load)	29,0 m/s
chain bar length	400 mm (16") / 450 mm (18") / 500 mm (20")
Chain Pitch	0,325 "
Chain Gauge	0,05 / 0,063 "
Chain Gauge	1,3 / 1,6 mm
Number of Drive Links	67 / 74 / 82
Chain Oil Tank	260 ml
Brushless Motor	✓
Vibration Level, Cutting Wood	4,1 m/s ²
Vibration Uncertainty (K Factor), Cutting Wood	1,5 m/s ²
Sound Pressure Level (L _{pA})	99 dB(A)

User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Main power switch with auto power-off function for battery saving and avoiding unintentional start up
- Variable speed control by trigger
- Adjustable automatic chain lubrication with large oil reservoir

Link to product - www.makita.uk.com



Related products

Optional AC

1915Y7-3

Guide Bar 16" / 40cm



1915Y8-1

Guide Bar 18" / 45cm



1915Y9-9

Guide Bar 20" / 500 mm



1916A1-3

Saw Chain 16" / 40cm, 95TXL



1916A2-1

Saw Chain 18" / 45cm, 95TXL



1916A3-9

Saw Chain 20" / 500 mm, 95TXL



4133H6-7

Guide Bar Case 535



4133L9-9

Guide Bar Case 465



Other

User manual

Parts drawing