

LC1D50G7

Contactor , Non-Reversing, 3-Pole (3 N.O.), TeSys,
Type: TeSys D



Technical Characteristics

Marketing Trade Name	TeSys
Inductive Amperes (AC3)	50A
Resistive Amperes (AC1)	80A
Approvals	UL Listed File E164862 CCN NLDX - CSA Certified File LR43364 Class 3211 04 - IEC Rated - CE Marked
Catalog Reference Number	8502CT9901
Horsepower Rating (1-Phase)	3HP@115VAC - 7.5HP@230VAC
Horsepower Rating (3-Phase)	15HP@200/230VAC - 40HP@460/575VAC
Action	Non-Reversing
Type	TeSys D
Terminal Type	Screw Clamp
Maximum Voltage Rating	600VAC
Operating Voltage	120VAC@50/60Hz
Number of Poles	3-Pole (3 N.O.)

Shipping and Ordering

Category	22345 -
Discount Schedule	I12
Article Number	785901421450
Package Quantity	1
Weight	3.1 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.