



Product data sheet

Power tools for trade & industry

Inspection Camera

PRO GIC 12V-4-23 C



High-resolution camera for quick and easy inspection and documentation

The most important data

Display resolution	800 Pixel x 480 Pixel
Display size	4.3 "
Length of camera cable	150 cm

Part Number 0 601 241 500

Technical data

Technical data

Display size	4.3 "
Display resolution	800 Pixel x 480 Pixel
Diameter of camera head	8.3 mm
Length of camera cable	150 cm
Field of view (FOV)	75°
Focus distance	30 - 80 mm
Documentation via	Photo
Photo resolution	1280 x 720
Data Transfer	USB-C®
Dust and splash protection, camera cable	IP 67
Dust and splash protection, tool	IP 54
Max. 30 min immersion for camera cable in	diesel, petrol, engine oil, AdBlue®, ethyl alcohol, salt water (26.5 % salt content)
Weight	0.7 kg



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- High resolution of 800 x 480 pixels ensures clear picture quality on big 4.3" screen
- The convenient Up Indication always points up for optimal user orientation
- Ideal on tough jobsites thanks to IP ratings for dust and water protection



PROTECTED TOOLS
Impact | Water | Dust



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

