

Slide Compound Mitre Saw XGT®

LS003G

40Vmax • 305 mm • 3 600 min⁻¹

Efficient brushless cordless saw with a remote start for dust extraction (AWS) for demanding use.

Powered by XGT® 40Vmax battery this brushless saw is extremely powerful. Equipped with single sliding system and rail-forward design enables saw to be placed against wall for maximizing work space. Mitre angles 60° and bevel angles 48°. Led light illuminates the working area.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Max. kerf thickness of the saw blade	3,2 mm
Brushless Motor	✓
Capacity 90°	107 x 363 / 92 x 382 mm
No load speed	3600 min ⁻¹
Capacity 45° left	71 x 363 / 61 x 382 mm
Max. Bevel Range (Left)	48 / 48 °
Max. Mitre Range (Left)	60 / 60 °
Sound Power Level (L _{WA})	100 dB(A)
Sound Pressure Level (L _{pA})	91 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	30,5 - 31,7 kg
Product Dimensions (L x W x H):	898 x 690 x 725 mm

User benefits

- High power delivered by 40V max Brushless motor enables to cut as fast as if you were using a corded slide compound Mitre saw
- Vacuum cleaner activation switch for increased comfort
- LED light with ink line aligning function
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Large turn base supports workpiece securely for increased stability
- Holders are provided on both sides of the tool to hold long workpieces horizontally
- Front knob for easy bevel angle adjustment
- Integrated guide fences for increased rigidity and high cutting accuracy
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing