


Mounting plate 3VA10 (100 A), 3VA11 (160 A), 3-pole, 8US setup, RCD: without,
H: 350 mm W: 800 mm



Model	
product brand name	SIVACON S4
General technical data	
surface processing	Galvanized
product feature perforated	Yes
Mechanical Design	
height	350 mm
width	800 mm
depth	400 mm
net weight	5.37 kg
material	sheet-steel
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



[Confirmation](#)

Environment

[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ6000-8BA40>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ6000-8BA40>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ6000-8BA40

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

