


111ER Reversible jaw adjustable wrenches with scales, chrome-plated

The new reversible jaw adjustable wrench, Beta 111ER, allows differently sized nuts and bolts to be tightened and loosened through the sliding jaw, which can be adjusted through the central roll; it can also be used to work on most commercially available pipes by turning the jaws, if need be.

Features:

- Head angled at 15 degrees, allowing hardly accessible spaces to be reached
- Reversible jaw for optimal hold, e.g. on pipes
- Compact head with completely open jaw
- Right-hand rotation
- Double laser marking in mm/inches
- Matt chrome-plated heads for improved scale readout
- Made from high-performance alloy steel for increased mechanical torsional strength
- Special heat treatment for excellent wear resistance
- Large handle for optimized comfort
- Hole on handle for hanging wrench

Reversible jaw

	art.	L mm	L "	A max mm	Ø max "	
001110520	111ER 200	200	8	29	3/4	275
001110525	111ER 250	250	10	34	1	402
001110530	111ER 300	300	12	40	1.1/4	707

