

WE1010 Set (UK) 230V

Item No: T0053298399

1-Channel Power Unit, digital, 70 W



KEY FEATURES

- + Power unit, 1 channel with soldering iron WEP70 and safety rest PH70
- + 70 W solder iron with ergonomic handle and providing toolless tip change
- + ESD safe station, iron and heat-resistant silicon cable for safe handling
- + Using ET soldering tips
- + Standby mode and auto setback conserves energy, protects equipment
- + Password-protected to preserve settings
- + Replacement for 4ETH, 4ETK, 4ETO, 4ETS necessary. For WEP 70 4ETHL, 4ETKL, 4EKOL and 4ETSL must be used.
- + Change hot tips out by hand by twisting the plastic knurled nut on the soldering pencil without an additional tool.

TECHNICAL DATA

Length	150mm
Dimensions L x W x H	150.0 x 120.0 x 98.0mm
Approximate Heating Time (50–350 °C/120–660 °F)	28 sec
ESD Safe	Yes
Number of Channels	1
Power	85 W
Temperature Accuracy °C	± 5°C
Temperature Accuracy °F	± 9°F
Temperature Range °F	200 - 850 °F
Temperature Stability °C	± 6°C
Temperature Stability °F	± 10°F
Tip Type	ET
UPC	4003019439980
Voltage	230V
Weight (Catalog)	1.90 kg
Product Family	WE Line Soldering Stations