

## FEATURES

- **Heat Stabilised Nylon:** Ensures durability in high-temperature environments up to 105 °C
- **UL 94 V-2 Fire Behaviour:** Provides flame retardant properties for added safety
- **18 kg Tensile Strength:** Offers strong and secure fastening for various applications
- **150 mm Length:** Suitable for bundling medium-sized cable groups
- **3.6 mm Width:** Balances flexibility and strength for versatile use

## RS PRO 150mm Nylon Cable Tie, Heat Stabilised

RS Stock No: 656-017



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

These RS PRO cable ties are designed for securing and organising cables efficiently. Made from durable nylon, they are heat stabilised, making them ideal for environments with fluctuating temperatures. With a maximum bundle diameter of 36 mm, they provide a reliable solution for cable management.

### General Specifications

Colour	Light Green
Product Type	Cable Tie
Sub Type	Heat Stabilised
Tensile Strength	18 kg

### Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	No

### Mechanical Specifications

Length	150 mm
Material	Nylon
Maximum Bundle Diameter	36 mm
Width	3.6 mm

### Operation Environment Specifications

Maximum Operating Temperature	105 °C
-------------------------------	--------

### Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---

