



R-259B

Waterproof heavy-duty impact gloves,
with advanced cut resistance for
assured hand safety



Impact

Abrasion Protection



Cut

Liquid Spray and Splash



Oil



Heavy Duty

Waterproof heavy-duty impact gloves, with advanced cut resistance for assured hand safety

- **Specialized protection:** RINGERS® R259B impact gloves' patented TPR (thermoplastic rubber) design, developed with F3 Technology™, provides knuckles, thumb and finger-length protection
- **Advanced defenses:** An additional palm layer enhances cut resistance, while a waterproof barrier and liquid-resistant coating at the top of the hand ensure dry, dependable personal protection
- **Optimized usability:** Their advanced construction includes a durable bond between each layer, limiting glove separation when doffing
- **Strengthened grip:** A synthetic leather palm ensures superb grip
- **Enhanced features:** These RINGERS® gloves increased visibility design, with reflective cuff piping, further enhances safety levels, while an extended neoprene wrist closure ensures a secure fit



Industries

- Manufacturing
- Oil and gas

Applications

- Engagement and release of drill string slips
- Chaining up pipes
- Facility and machinery maintenance
- Installation and dismantling of rigs
- Handling iron
- Operating of heavy machinery
- Equipment maintenance and repair
- Pipe handling
- Handling materials with sharp or rough edges
- Loading and hauling
- Hydraulic repair
- Re-fuel oil fluid and diesel



R-259B

Waterproof heavy-duty impact gloves,
with advanced cut resistance for
assured hand safety

Key Features

- **Patented TPR design:** Knuckles, thumb and finger-length impact protection
- **Waterproof barrier and liquid-resistant coating:** For safe, dry hands
- **Additional palm layer:** Advanced cut resistance capabilities

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X44FP

EN 511



021

ANSI/ISEA 138-2019



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COATING COLOR	PACKAGE
RINGERS® R259B	Liner Material: HPPE Cuff Style: Extended neoprene wrist closure		8, 9, 10, 11, 12, 13	Red	5 pairs/bag, 10 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

