



Main

Product or component type	Double OC contact
Range of product	NG125
Device short name	OF and OF
Signal contacts composition	2 C/O
9 mm pitches	1

Complementary

[Ui] rated insulation voltage	690 V AC 50/60 Hz conforming to EN/IEC 60947-5-1
[Uimp] rated impulse withstand voltage	8 kV conforming to EN/IEC 60947-5-1
Mounting mode	Fixed
Mounting support	DIN rail
Height	103 mm
Width	18 mm
Depth	69 mm
Electrical durability	10000 cycles conforming to EN/IEC 60947-5-1
Connections - terminals	Plate terminal 2 rigid cable(s) 2.5 mm ² max Plate terminal 2 flexible cable(s) 2.5 mm ² max Plate terminal 1 rigid cable(s) 2.5 mm ² max Plate terminal 1 flexible cable(s) 2.5 mm ² max
Wire stripping length	10 mm
Tightening torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C

Contractual warranty

Period	18 months
--------	-----------