

Eaton 24FDIHA10

Catalog Number: 24FDIHA10

Eaton Bussmann series medium voltage BS air fuse, 10 A, AC 22 kV, 51 x 565 mm, fullrange, BS, with striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage BS air fuse	24FDIHA10
	EAN
	5027590468893
Product Length/Depth	Product Height
565 mm	50.8 mm
Product Width	Product Weight
50.8 mm	2573 g
Compliances	Certifications
BS 2692-1	KEMA Certified

Product specifications

Resources

Used with

A3354710 Fuse clip

Type

fuse

Application

protection of primary side
transformers
used in fuse switch
combination units, fuse
bases and fuse switches

Amperage Rating

10 A

Fuse size

50.8 x 565 mm

Breaking capacity

35.5 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Full-range

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

British Standard

Utilization category

Other

Voltage type

AC

With striker

Yes

Class

Class full-range

Fuse shape

Cylindrical

Pre arc (I2T)

2.7 x 102

Resistance

205 ohms

Fuse diameter

51 mm

Interrupt rating

35.5 kAIC

Construction size

51 x 565 mm

Mounting method

Clip-in

Voltage rating

24 kV

Fuse type

FDIH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia