

Technical data sheet

Article number:
924-00535

3R12

Product Group	Ring Terminals
Product Family	Single Grip Pre-Insulated
Material	Copper (CU), Polyvinylchloride (PVC)
Colour	Yellow (YE)
Application Range	Low Voltage
Conductor Size Range mm ²	4.0-6.0 mm ²
Diameter (D)	6.7 mm
for Hole Ø (FH)	13.0 mm
Length (L)	39.1 mm
Length (L2)	13.6 mm
Length (L3)	25.5 mm
Max Current	48 A
Max Voltage	600 V
Operating Temperature	+75 °C
Package Content	50 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	19.2 mm

RoHS 