




NOTES:

- 1 ATTENUATION $\leq 0,5$ dB(MT-RJ) AND $\leq 0,3$ dB(ST),
MEASURED AT 1300nm ACC. TO IEC 61300-3-4
EQUILIBRIUM MODE CONDITION
- 2 INDIVIDUAL LENGTH DIFFERENCE ON SC SIDE ≤ 50 mm
- 3 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH
INDIVIDUALLY PACKED ASSEMBLY
- 4 DAT LABEL INFO:
 - UNIQUE SERIAL NUMBER
 - TYCO LOGO PN
 - MANUFACTURING LOCN.
- 5 ADD CABLE ATTENUATION OF 1,5dB/Km AT 1300nm
- 6 CROSS OVER AS PER BELOW TABLE

FIBRE COLOR	LEFT CONN.	RIGHT CONN.
WHITE	ST RED	MT-RJ B
BLUE	ST BLACK	MT-RJ A

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-6206616-Y	XY,0
9-6206616-9	100,0

1	—	DAT-85 LABEL	15
1	—	DUST COVER, MT-RJ	14
1	—	HOUSING, CONN, MT-RJ,BLACK	13
1	—	MT/RJ FERRULE, THERMOPLAST,MM	12
1	—	PIN KEEPER, 3.8MM	11
1	—	SPRING, MT-RJ, 3.8 DESIGN	10
1	—	MT-RJ, SPRING PUSH, UNIVERSAL	9
1	—	CRIMP EYELET, MT-RJ	8
1	—	MT-RJ BOOT, TWIN ZIP BEIGE	7
2	—	PROTECTIVE COVER, 2.5MM, BLACK	6
2	—	ST CERAMIC, OVERMOLDED	5
2	—	FOAC CRIMP EYELET 2.0	4
1	—	FOAC BOOT 2.0 BLACK SC/FC	3
1	—	FOAC BOOT 2.0 BLACK SC/FC	2
L	—	FOCAB 1.8MZ T 62.5/125 GREY LSZH	1
Qty	Part Number	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
—

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±	—
1 PLC	±	—
2 PLC	±	—
3 PLC	±	—
4 PLC	±	—
ANGLES	±	—
FINISH	—	—

25 AUG 05
GIRIYAPPA. M

25 AUG 05
DIWAKAR BELAVADI

25 AUG 05
DIWAKAR BELAVADI

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

25 AUG 05
GIRIYAPPA. M

25 AUG 05
DIWAKAR BELAVADI

25 AUG 05
DIWAKAR BELAVADI

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics Corporation
FOBU, Bangalore, India

NAME
FORM 62,5 LEAD 1,8 MZ DPX ST-MTRJ

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=6206616

RESTRICTED TO
—

SCALE
NTS

SHEET
1

OF
1

REV
A

AMP 1471-9 REV 31MAR2000