

Product datasheet

Specifications



Thorsman Glands - cable gland - grey - M20 - diameter 6 to 12

ISM71503

EAN Code: 3606480077203

Price: 1,46 EUR

Main

product range	Thorsman Glands
product type	Cable gland
colour	Grey (RAL 7035)
quantity per package	Set of 20

Complementary

Material	PA6
ISO thread	M20
Cable outer diameter	6...12 mm

Environment

IP-Class	IP68
operating temperature	-30...80 °C permanently -30...150 °C intermittently

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	3.000 cm
Package 1 Length	4.000 cm
Package 1 Weight	11.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	4.000 cm
Package 2 Width	20.000 cm
Package 2 Length	25.000 cm
Package 2 Weight	220.000 g
Unit Type of Package 3	CAR
Number of Units in Package 3	1100
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm

Rates duty January 2016

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Length	60.000 cm
Package 3 Weight	12.100 kg

Contractual warranty

Warranty	18 months
----------	-----------




Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.


[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No

Use Again

 Repack and remanufacture	
Take-back	No