

RS Pro Datasheet – Fiche Technique – Datenblatt


RS Pro: 144-8591





VALUE USB 2.0 Cable, A - Micro B, M/M, 3.0m

VALUE Câble USB 2.0, USB A mâle - Micro USB B mâle, 3,0m


VALUE USB 2.0 Kabel, USB A ST - Micro USB B ST, 3,0m



MARKING: AWM E200765 STYLE 2725 60°C 30V 1P/28AWG AND 2C/28AWG USB FT2



Pin Assignment



ITEM NO	QTY	DESCRIPTION	COLOR
11.99.8752	10	VALUE USB2.0 Cable, TypeAM-Micro BM, 1.8m	white
11.99.8754	10	VALUE USB2.0 Cable, TypeAM-Micro BM, 0.8m	white
11.99.8755	10	VALUE USB2.0 Cable, TypeAM-Micro BM, 3.0m	white

Note:

1. Conductor material: Bare copper
2. Braid material: AL-MG braiding
3. Drain material: Tinned copper wire

④	MOLDING	OUTER MOLD: 45P PVC COLOR, white	9	G
③	USB-MICRO B	USB MICRO B MALE CONNECTOR FLASH GOLD ; NICKEL PLATED SHELL	1	SET
②	USB-AM	USB AMALE CONNECTOR FLASH GOLD ; NICKEL PLATED SHELL	1	SET
①	CABLE	USB CABLE 28AWG/1P+28AWG/2C+AL+BRAID (48*0.12mm AL-MG braiding) +Drain(7*0.12 Tinned copper wire)PVC JACKET OD: 3.8 ± 0.2mm , COLOR: WHITE 433#	L	M
NO	P/N	DESCRIPTION	QTY	UNIT

REMARK NO	CHANG	SIGNATURE	DATE
DRAWN BY	MORGAN		
CHECKED BY			
AUDITED BY		APPROVED BY	QIJUNJIAN
DRAFT		DATE	2010.12.30

SIGN	WT	SCALE
PAGE OF		