

# D-TB 2,5-BCVP/1P - Cover



3247117

<https://www.phoenixcontact.com/fr/products/3247117>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover, depth: 35.9 mm, width: 2.4 mm, height: 44.3 mm, color: dark gray

## Commercial data

Item number	3247117
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BEKZ1X
Product key	BEKZ1X
GTIN	4046356713924
Weight per piece (including packing)	2.14 g
Weight per piece (excluding packing)	2.14 g
Customs tariff number	85389099
Country of origin	PL

# D-TB 2,5-BCVP/1P - Cover



3247117

<https://www.phoenixcontact.com/fr/products/3247117>

## Technical data

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

### Material specifications

Color	traffic grey B (RAL 7043)
Material	PA
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

### Dimensions

Width	2.4 mm
Height	44.3 mm
Depth	35.9 mm

# D-TB 2,5-BCVP/1P - Cover

3247117

<https://www.phoenixcontact.com/fr/products/3247117>



## Classifications

### ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

### ETIM

ETIM 9.0	EC000886
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# D-TB 2,5-BCVP/1P - Cover

3247117

<https://www.phoenixcontact.com/fr/products/3247117>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT SAS  
52 Boulevard de Beaubourg Emerainville  
77436 Marne La Vallée Cedex 2 France  
+33 (0) 1 60 17 98 98  
[documentation@phoenixcontact.fr](mailto:documentation@phoenixcontact.fr)