



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 1-5221128-7 PLUG,COMMERCIAL BNC	 TE Part # 5413959-3 BNC HEX RT ANG PLUG 50 OHM	 TE Part # 5227079-1 COMM BNC PLUG	 TE Part # 2-5221128-3 PLUG,COMMERCIAL BNC
 TE Part # 5225395-8 BNC PLUG DUAL CRIMP RG179, 187	 TE Part # 8-5227079-2 COMM BNC PLUG	 TE Part # 4-5225395-2 PLUG,DUAL CRIMP, BNC	 TE Part # 1-5221128-0 PLUG,COMMERCIAL BNC
 TE Part # 1-329631-2 JAM NUT, PLATED	 TE Part # 1-5227079-6 COMM BNC PLUG	 TE Part # 5225395-1 BNC PLUG DUAL CRIMP RG58,A,B,C	 TE Part # 5227079-2 COMM BNC PLUG
 TE Part # 1-5227079-1 COMM BNC PLUG	 TE Part # 1-329632-2 LOCKWASHER, PLATED	 TE Part # 5225395-6 BNC PLUG DUAL CP RG142	 TE Part # 5227079-7 COMM. BNC-PLUG
 TE Part # 5227079-6 COMM. BNC-PLUG	 TE Part # 1-1337524-0 BNC Plg DCap & Chn Nickel Pltd	 TE Part # 5227079-5 COMM BNC PLUG	 TE Part # 2-5330061-1 BNC PLUG

Customers Also Bought



TE Part #YDTS33F15NV0010000
DUST COVER ASSEM



TE Part #YDTS33F11RV0010000
DTS CAP ASSY, NICKEL, SIZE 11 RCPT



TE Part #D369-R33-NP1
369 3 WAY REC, CRIMP, PIN



TE Part #620001-000
D-100-00



TE Part #227699-2
BNC PCB VERTICAL



TE Part #1054869-1
2084 0000 02



TE Part #1-1393118-7
KUP-14D15-48=KU



TE Part #1-1478763-5
METAL BACKSHELL 15 WAY 45 DE



TE Part #6609021-1
1VB1=F7120 S0

Documents

Product Drawings

JACK,ADAPTER,BHD,ISOLATED BNC

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_5414105-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_5414105-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_5414105-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



BNC Connectors

English