2504 : Copper Forming Set



Description

For annealed copper pipes.

The holes in the die have a 90° chamfer on one side for forming tapered flanges with the turn pin.
The other side may be used for forming flat flanges after first forming a tapered flange.
4 opposing pegs are provided for securing the die in a parallel vice.
Phosphate finish.
Supplied in a plastic case with turn pin plus single and stepped mandrels.





References

Sku	Composition of set	kg
250401	Die for pipe O.D. : 6 - 8 - 10 - 12 - 14 mm, 90° turn pin for pipe O.D. : 6 to 14 mm, Single size mandrel 10 to 12 mm dia, Stepped mandrels 8 to 14 mm	1,350
250402	Die for pipe O.D. : 10 - 12 - 15 - 16 - 18 - 20 - 22 mm, 90° turn pin for pipe O.D. : 10 to 22 mm, Single size mandrel 16 mm Ø.Stepped mandrels 10 and 18, 12 and 20 and 15 and 22 mm Ø.	3,440
250403	Die for pipe O.D. : 10 - 12 - 14 - 16 - 18 - 20 - 22 mm, 90° turn pin for pipe O.D. : 10 to 22 mm, Single size mandrel 16 mm Ø, Stepped mandrels 10 and 18, 12 and 20 and 14 and 22 mm Ø.	3,400

