


ENCOREPRO 700 SERIES

Expect more. Deliver more.

With customer expectations continuing to rise and calls are becoming more complex than ever, accept no compromises with the premium EncorePro. Offer your people the ultimate in comfort, audio quality and reliability with our top-of-the-range headset and help them deliver smarter customer interactions. Featuring seven axes of adjustability plus an exclusive extendible mic boom and three-year warranty, the premium EncorePro is the ultimate headset for all-day calling. With a choice of monaural and binaural wearing styles, its sophisticated over-the-head design coupled with a lightweight yet robust construction and VoIP-ready wideband audio make this the most advanced EncorePro ever made.



HW720 Binaural



HW710 Monaural



Performance by design



ENCOREPRO 700 SERIES

KEY FEATURES

- Enhanced noise-cancelling and wideband audio give you clearer conversations with your customers enabling you to offer a better service
- Distinctive and unique design provides high performance and a stylish look
- Slim and discrete construction ensures comfort and allows you to fully focus on the customer
- VoIP ready through the use of enhanced echo control and wideband audio, allows you to preserve your investment through future phone system upgrades
- Seven axes of adjustability ensure you can wear the headset in the most comfortable and effective position
- Quick Disconnect feature provides walkaway convenience and compatibility with all Plantronics® USB and deskphone audio processors and direct connect cables
- Backed by industry-leading Plantronics global service and support

HW710/HW720

- Quick Disconnect for multiple connectivities and walkaway convenience
- Re-enforced, lightweight headband provides strength and durability
- Plush leatherette ear cushions for all-day comfort
- Wideband audio for higher quality calls
- 3 year warranty



Performance by design



Connects to	PC or deskphone with Plantronics audio processors
Ideal for	Telephone intensive users in roles that warrant premium comfort, traditional formal contact centres and informal contact centres (e.g. helpdesks)
Audio performance	Wideband audio (up to 6,800 Hz), noise-cancelling microphone

Transmit Characteristics (typical)

Sensitivity @ 1kHz:	-39 ± 3 dBV/Pa
Frequency Range:	150 to 6800Hz
Output Impedance:	<125Ω
Typical Test Conditions:	1.8VDC, 3.3KΩ DC Resis, 3.3KΩ AC Load

Receive Characteristics (typical)

Sensitivity @ 1kHz:	17 dBPa/V (Monaural) 10 dBPa/V (Binaural)
Frequency Range:	100 to 6800Hz
Acoustic Limit:	<24dBPa (<118SPL)
Input Impedance:	150Ω ± 25% (Monaural) 300Ω ± 25% (Binaural)
Typical Test Conditions:	100mV Drive, 10Ω Source Impedance. Measured on ITU-T Type 3.3 artificial ear, Ear Reference Point

Headset	Model	Weight	Part number
HW710, EMEA	Over-the-head, Monaural, Noise-cancelling	50g	78712-102
HW720, EMEA	Over-the-head, Binaural, Noise-cancelling	72g	78714-102

For more information about the HW710/HW720 or other products, please visit our website at plantronics.com.

GLOBAL SERVICE AND SUPPORT

Backed by Plantronics industry-leading global service and support.

Plantronics Ltd, Royal Wootton Bassett, UK, 0800 410014 or +44 (0)1793 842200

Connect with Plantronics

