



### Main

Range	Merten
Product or component type	Switch
Device application	Lighting
Device presentation	Mechanism with fixing frame
Technology type	Electromechanical
Device mounting	Flush
Number of rocker	1
Actuator	Rocker

### Complementary

Switch function	1-pole 2-way
Local signalling	LED
Signalling function	Indicator
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Rated current	10 AX
Connections - terminals	Screwless terminals
Fixing mode	By screws and claws

### Environment

IP degree of protection	IP20
-------------------------	------

### Offer Sustainability

Sustainable offer status	Green Premium product
Cradle to Cradle	Silver
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins