

FEATURES

- Momentary foot switch controller
- Contact rating 10A 250Vac DPDT snap action
- Orange cast aluminum construction
- Protective shield
- Rated to IP68 – protected from dust and water
- Single PG16 threaded conduit entry
- 3 fixing holes for floor or equipment mounting

RS PRO Momentary Heavy Duty Foot Switch - Aluminium Case Material, DP-CO, 3 A @ 240 V ac, 6 A @ 125 V ac Contact

RS Stock No.: 116-776



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

RS PRO heavy duty foot switch comes with a shield for extra safety and has DPDT snap action contacts. This foot controller pedal is orange in colour and is constructed from aluminium. This foot switch can also be mounted securely to the floor or on equipment for extra protection.

General Specifications

Contact Configuration	DP-CO
Switch Operation	Momentary
Case Material	Aluminium
Switch Environment	Heavy Duty
Guard Cover	Yes
Colour	Orange
Applications	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps
Cable Connection	1 off M20 entry

Electrical Specifications

Contact Voltage Rating (AC)	240V
Contact Voltage Rating (DC)	250V
Contact Current Rating	3A @ 240 V ac, 6A @ 125V ac

Mechanical Specifications

Length	231.9mm
Height	136.4mm
Dimensions	231.9mm x 153.16mm x 136.4mm
Width	153.16mm
Weight	2.4kg

Protection Category

IP Rating	IP68
------------------	------

Approvals

Standards Met	EN 60529
Compliance/Certifications	CE, RoHS





Size

(See below)

