

## **Datasheet**

**ENGLISH** 

Stock No: 564-481

# RS Pro Telephone Slide Filament Indicator Lamp, Clear, 48 V, 25 mA, 5000h



### **Product Details**

#### T5.5 Telephone Slide

Filament lamps will perform to specification and give optimum life when:

- a) They are powered at the rated voltage from a stabilised 50 Hz AC supply.
- b) Ambient temperature is in the range 20°C to 25°C.
- c) No mechanical vibration is present.

Deviations from these criteria have a significant effect on lamp life, particularly with low current filaments (<80mA). Power from a DC supply at the rated voltage can reduce the listed life by up to 50%.

The effect of deviation from the rated operating voltage should be noted:

5% above will reduce lamp life by up to 50%.

5% below will significantly increase lamp life.

Power consumption may vary up to ±10% compared to the listed values at the rated supply voltage. Therefore particular care should be taken when a number of lamps are connected in series. In such applications it is recommended that the rated voltage be reduced by 10% to prevent premature failure of individual lamps.



## Specifications:

# ENGLISH

Voltage Rating	48 V
Lamp Base	Telephone Slide
Current Rating	25 mA
Diameter	5.4mm
Lamp Size	T5.5
Length	30 mm
Lens Colour	Clear
Luminosity	2.5 lm
Life Hours	5000h