



ENGLISH

Datasheet

RS Pro Double Sided Tissue Tape 100 micron

RS Stock No: 125-4302



Product Description

The RS Pro double sided paper tape uses tissue paper as the carrier. It is coated with excellent and extremely aggressive acrylic adhesive, protected by easy release double sided release liner.

Features

- Extremely Aggressive Adhesive
- Good Initial Tack
- Excellent Peel Adhesion
- Good Permanent Bonding

Applications

1. Poly bags and envelope sealing
2. Photos, posters, public notes sticking
3. Daily life usages
4. Paper relates products connecting and bonding

Property	Unit	Value	Test Method
Total Thickness	Micron	100	PSTC-33 / ASTM D3652
Peel Adhesion	N/25mm	18	PSTC-1 / ASTM D3330
Tack Rolling Ball	cm	10	PSTC-6 / ASTM D3121
Tensile Strength	N/25mm	40	PSTC-31 / ASTM D3759
Elongation	%	3.5	PSTC-31 / ASTM D3759
Service Temperature	°C	-20 ~ +80	-----
Applying Temperature	°C	+10 ~ +40	-----

Jumbo Roll: 1040mm x 1000m; 1040mm x 800m

Notes

1. The above data is typical results and subject to change without notice.
2. Tolerance: Weight and Thickness: $\pm 10\%$; Width: $\pm 3\text{mm}$; Length: Cut Roll: $\pm 0.3\text{m}$, Jumbo Roll $\pm 0.5\%$
3. The product should be stored at room temperature and kept from wet and heat source. Shelf life: One year from shipment date when stored at 21°C (70°F) / 50% relative humidity out of direct sunlight.
4. It is essential, as with all pressure sensitive tapes, that the surface to which the tapes is applied must be clean, dry and free of grease and oil.
5. The user should test and do a trial application on the above products before application to ensure the suitability for your specific purpose and technique.