



## New P1-40 Switch-disconnectors

Eaton's P1-40 Switch-disconnectors bridges the gap between the P1's previous maximum rating of 32 A and the P3's lowest rating of 63 A. It allows for a greater current rating in the compact P1 size.



P1-40/EA/SVB/HI11  
Main switch with auxiliary contacts



P1-40/I2H/N  
Surface mounting, switch fitted in polycarbonate  
Ci-K Enclosure with metric knockouts

### Technical data

- Rated current: 40 A
- Rated voltage: 690 V a.c.
- Utilisation categories: AC-21, AC-22, AC-23 and AC-3
- IEC/EN 60947 and IEC/EN 60204

### Features and benefits

- Compact solution with a 40 Amp current rating allows for higher power applications, future proofing your installation
- Variety of mounting and configuration options available to suit the majority of applications
- Compatible with all existing P1 accessories
- Set of four fork terminals included in box as standard for Main switches and enclosed switches for connection to the additional earth and neutral terminals to accommodate the larger wire sizes at 40 A, ensuring ease of installation



*Powering Business Worldwide*