



## Selection of 236 tools in foam module

### CPP-236MM

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:53:04



**DESCRIPTION****Selection of 236 tools in foam module**

Selection for the agricultural or civil engineering equipment maintenance technician. Perfect for carrying out interventions on civil engineering and agricultural machines and equipment requiring large tools.

**SPECIFIC DATA**

Designation	PUBLIC WORKS KIT IN FOAM MODULE
Sales reference	CPP-236MM

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>



Weight (kg)	26.500
Guarantee	O   SAM TOOL guarantee.










**Guarantee applied**

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

**Toolset**

	x 1	10-impact tool foam module <b>M1-10MM</b> Ref : M1-10MM
	x 1	Bodyworker's chisel <b>1-...</b> Ref : 1B
	x 1	Punch 10 mm <b>8N-...A</b> Ref : 8N-3A
	x 1	Constant section cape chisels <b>4-...-A</b> Ref : 4-200-A
	x 1	SAMSOPLUS® riveting hammer, three-material handle <b>310-...TM</b> Ref : 310-32TM
	x 1	Mallets with interchangeable tips <b>320-...D</b> Ref : 320-32D
	x 5	Long drift punches <b>7-...A</b> Ref : 7-25A -- 7-35A -- 7-50A -- 7-70A -- 7-90A
	x 1	MODULOSAM® for hammers and stamping tools <b>MOD-64</b>
	x 1	Foam module 1/3 with 12 combination spanners 8 to 22 mm <b>50N-J12MM</b> Ref : 50N-J12MM















**SAM Outillage**















10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France















RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-



<https://www.sam-outillage.com/>



		x 12	Extra-thin combination wrench <b>50N-...</b> Ref : 8 - 9 - 10 - 11 - 12 - 13 - 14 - 16 - 17 - 19 - 21 - 22 mm
		x 1	MODULOSAM® for combination wrenches <b>MOD-59</b> Ref : MOD-59
		x 1	Foam module 1/3 with 4 pliers, polished chrome-plate <b>P13-J4MM</b> Ref : P13-J4MM
		x 1	Polished chrome-plated stacked-branch multigrip pliers <b>209-25B</b> Ref : 209-25B
		x 1	Vice-grip, 45 - 50 mm opening <b>212-22</b> Ref : 212-22
		x 1	Polished chrome-plated universal pliers <b>204-...G</b> Ref : 204-18G
		x 1	Chrome-plated polished diagonal cutting pliers <b>232-...G</b> Ref : 232-16G
		x 1	Empty foam module 1/3 for 1 multigrip pliers + 1 vice-grip <b>MOD-63</b>
		x 1	Foam module 2/3 sawing <b>690-J5MM</b> Ref : 690-J5MM
		x 1	Double tip scriber <b>665-1</b> Ref : 665-1
		x 1	Flexible rules <b>781-...</b> Ref : 781-3
		x 1	Short measures with twin-material casings <b>UB-...</b> Ref : UB-519
		x 1	Lever type SAMSOCUT® metal saw <b>791</b> Ref : 791
		x 10	Hss bi-metal opticut metal saw blades <b>691-...A</b> Ref : 691-E10A

	x 1	18 leds 180° magnetic inspection lamp <b>2953R</b> Ref : 2953R
	x 1	Electrician's cable stripper knife <b>370-2</b> Ref : 370-2
	x 1	Empty foam module 1/3 for sawing accessories <b>MODM-32</b> Ref : MODM-32
	x 1	Foam module 1/3 with male keys and accessories <b>62-R72MM</b> Ref : 62-R72MM
	x 9	Rack of 9 hexagonal keys <b>62-R9A...</b> Ref : 62-R9A
	x 9	Rack of 9 Torx® male keys <b>66-R9A</b>
	x 9	Rack of 9 male 6-flat keys with spherical head in mm <b>67-AR9A</b> Ref : 67-AR9A
	x 9	Rack of 9 Resistorx® male keys <b>59-R9A</b> Ref : 59-R9A
	x 9	Rack of 9 long 6-flat male keys 1/4" <b>63-R9A...</b> Ref : 63-R9A
	x 1	Self-retracting blade knife <b>378-40</b> Ref : 378-40
	x 1	Padlock <b>CAD-...</b> Ref : CAD-25
	x 1	Universal hand shears <b>331-16</b> Ref : 331-16
	x 5	Set of 5 helix pullers <b>761-C-5</b> Ref : 761-c-5
	x 1	Pen light <b>1396-LS</b> Ref : 1396-LS

	x 1	1/4" socket holder <b>EVC</b> Ref : EVC
	x 1	Satin-finish adjustable wrenches <b>54-C...</b> Ref : 54-C10
	x 1	Empty foam module 1/3 for accessories <b>MODM-11</b> Ref : MODM-11
	x 1	Foam module 1/3 with 6 combination spanners <b>50N-J6MM</b> Ref : 50N-J6MM
	x 6	Extra-thin combination wrench <b>50N-...</b> Ref : 22 - 24 - 27 - 29 - 30 - 32 mm
	x 1	Empty foam module 1/3 for large wrenches <b>MODM-29</b> Ref : MODM-29
	x 1	Foam module 1/3 with 6 tools 3/4" in mm <b>78-C6MM</b> Ref : 78-C6MM
	x 1	Centre reversion 3/4" ratchet <b>C-150</b>
	x 1	Handle for c-150 ratchet and c-140 joint handle <b>C-125-A</b>
	x 1	Sliding 3/4" locking handle <b>C-120A</b>
	x 2	3/4" extensions <b>C-2...</b> Ref : C-208 - C-215
	x 1	3/4" joint <b>C-240</b>
	x 1	Empty foam module 1/3 for accessories 3/4" <b>MODM-14</b>
	x 1	Foam module 1/3 with 17 tools 3/4" 6-flat in mm <b>78-CH17MM</b> Ref : 78-CH17MM

	x 18	3/4" short hexagonal sockets in mm <b>CH-...Douilles_3/4_MM</b> Ref : 22 23 24 26 27 29 30 32 35 36 38 41 42 46 50 54 55mm
	x 1	Empty foam module 1/3 for sockets 3/4" <b>MODM-15</b>

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:53:04

