



Product data sheet

Power tools for trade & industry

Polisher

PRO GPO 14-180 S



Excellent performance and outstanding comfort

The most important data

Rated input power	1,400 W
No-load speed	3,500 rpm
Polishing sponge, diameter	180 mm

Part Number 0 601 389 270

Technical data

Technical data

Rated input power	1,400 W
No-load speed	3,500 rpm
Power output	825 W
Grinding spindle thread	M14
Rubber sanding plate, diameter	150 mm
Polishing sponge, diameter	180 mm
Weight	2.3 kg
Packaging dimensions (width x length x height)	195 x 585 x 100 mm
Voltage, electrical	220 V
Main handle	Rattail

Noise/vibration information

Polishing

Vibration emission value ah	2.4 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Excellent performance thanks to 1400 W input power; High comfort, low fatigue: lightweight design and low vibration makes prolonged polishing easy; Outstanding protection with soft start, overload and restart protection and improved dust filter; Comfortable and convenient with soft grasp and ergonomically positioned switch, handle and speed dial; Precision work thanks to progressive trigger and 6-level speed selection

**HEAVY
DUTY**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

