

✔ Allsafe Household (UGHG300**)

cotton flock-lined · 4 colours · medium weight · latex reusable household gloves

Physical Specifications:

Material: Latex
Colours: Blue, Green, Pink, Yellow
Length: 300 mm
Weight: 28.0 g
Thickness: 0.31 mm
Finish: Flock lined

Order Codes and Size Information:

UGHG3002* | Small
UGHG3003* | Medium
UGHG3004* | Large
UGHG3005* | Extra large
* B = Blue / G = Green / P = Pink / Y = Yellow

Packaging:

1 pair per polybag
12 pairs per master polybag
12 master polybags per case

Classification:



For minimal risks only

🔗 Features


- Available in four colours
- Cotton flock lined
- Anatomically shaped and tapered at the wrist
- Beaded cuff
- Manufactured with diamond textured palms and fingertips
- Medium-weight construction

🔗 Benefits

- Ideal for colour-coding in food, cleaning and healthcare environments
- Soft flock lining helps keep hands feeling cool and dry
- Anatomically shaped for a more comfortable and ergonomic fit
- Beaded cuff provides extra strength during donning and helps prevent liquid roll back
- Diamond textured palms and fingertips provide improved grip, particularly when working in wet or oily conditions
- Medium-weight construction provides a balance of strength and sensitivity

🔗 Sectors

- Care home work
- Cleaning and janitorial
- Food processing
- General assembly
- Janitorial
- Light duty maintenance
- Local Authority work



full palm & finger texture

For more about the Allsafe range, please click on the image



UNIGLOVES UK
Registered in England No: 4010200
VAT registration 791817787

📍 3 Ambley Green, Gillingham Business Park, Gillingham, ME8 0NJ, UK
☎ +44 (0)800 049 6602
✉ enquiries@unigloves.co.uk
🌐 unigloves.co.uk

UNIGLOVES GERMANY
Arzt- & Klinikbedarf
Handelsgesellschaft mbH

📍 Camp-Spich-Straße 71
D-53842 Troisdorf-Spich,
☎ +49 (0) 2241-9323-0
✉ unigloves@unigloves.de
🌐 unigloves.de

