RS Pro 17mm IP68 Connectors - with Solder Terminals



(please see pages 2 & 3 for details of parts with crimp terminals - all types are intermatable)

Cabl	e-Mount Conne	ector		In-Lin	e Cable Conne	ctor		Rear-Nut Panel-Mount Connector			
		Section 1									
RS Stock No:	No. of Contacts	Gender	1	RS Stock No:	No. of Contacts	Gender		RS Stock No:	No. of Contacts	Gender	
144-4179	2	Female	Mates with	144-4158	2	Male	Or	144-4172	2	Male	
144-4180	3	Female	"	144-4159	3	Male	"	144-4173	3	Male	
144-4181	4	Female	"	144-4160	4	Male	"	144-4174	4	Male	
144-4182	5	Female	"	144-4161	5	Male	"	144-4175	5	Male	
144-4183	7	Female	"	144-4162	7	Male	"	144-4176	7	Male	
144-4184	9	Female	"	144-4163	9	Male	"	144-4177	9	Male	
144-4185	10	Female	"	144-4164	10	Male	"	144-4178	10	Male	
144-4186	2	Male	Mates with	144-4151	2	Female	Or	144-4165	2	Female	
144-4187	3	Male	"	144-4152	3	Female	"	144-4166	3	Female	
144-4188	4	Male	"	144-4153	4	Female	"	144-4167	4	Female	
144-4189	5	Male	"	144-4154	5	Female	II .	144-4168	5	Female	
144-4190	7	Male	"	144-4155	7	Female	II .	144-4169	7	Female	
144-4191	9	Male	"	144-4156	9	Female	"	144-4170	9	Female	
144-4192	10	Male	"	144-4157	10	Female	"	144-4171	10	Female	
No s	ealing cap avail	able		Use Sealing Cap No: 207-0652	9			Use Sealing Cap No: 207-0652		_	

Connector Sets (Cable-Mount Socket & In-Line Plug)							
RS Stock No: No. of Contacts							
207-0649	2	Equivalent to 144-4186 Plug + 144-4151 Socket					
207-0650	3	Equivalent to 144-4187 Plug + 144-4152 Socket					
207-0651	4	Equivalent to 144-4188 Plug + 144-4153 Socket					
144-4217	5	Equivalent to 144-4161 Plug + 144-4182 Socket					
144-4218	7	Equivalent to 144-4162 Plug + 144-4183 Socket					
144-4219	9	Equivalent to 144-4163 Plug + 144-4184 Socket					
144-4220	10	Equivalent to 144-4164 Plug + 144-4185 Socket					



RS Pro 17mm IP68 Connectors - Supplied with Crimp Terminals

Cable-Mount Connector (Supplied with Crimps)					e Cable Connect olied with Crimp			Rear-Nut Panel-Mount Connector (Supplied with Crimps)				
											Crimp	o Details
RS Stock No:	No. of Contacts	Gender		RS Stock No:	No. of Contacts	Gender		RS Stock No:	No. of Contacts	Gender	Current Rating	Wire Size
124-6658	2	Female	Mates with	124-6649	2	Male	Or	124-6655	2	Male	10A	16 AWG
124-6659	3	Female	"	124-6650	3	Male	"	124-6656	3	Male	10A	16 AWG
124-6660	4	Female	"	124-6651	4	Male	II .	124-6657	4	Male	5A	24-20 AWG
124-6661	2	Male	Mates with	124-6646	2	Female	Or	124-6652	2	Female	10A	16 AWG
124-6662	3	Male	"	124-6647	3	Female	"	124-6653	3	Female	10A	16 AWG
124-6663	4	Male	"	124-6648	4	Female	II .	124-6654	4	Female	5A	24-20 AWG
No sealing cap available			Use Sealing Cap No: 207-0652	8	/		Use Sealing Cap No: 207-0652		/			

Connector Sets (Cable-Mount Plug & In-Line Socket)							
RS Stock No:	No. of Contacts						
124-6691	2	Equivalent to 124-6661 Plug + 124-6646 Socket (Includes Crimps)					
124-6689	3	Equivalent to 124-6662 Plug + 124-6647 Socket (Includes Crimps)					
124-6690	4	Equivalent to 124-6663 Plug + 124-6648 Socket (Includes Crimps)					

RS Pro 17mm IP68 Connectors - Shell only



(Crimp Terminals to be ordered seperately)

	e-Mount Conne Crimps Ordered			In-Line Cable Connector (Shell only - Crimps Ordered Separately)			Rear-Nut Panel-Mount Connector (Shell only - Crimps Ordered Separately			
RS Stock No:	No. of Contacts	Gender		RS Stock No:	No. of Contacts	Gender		RS Stock No:	No. of Contacts	Gender
181-1440	2	Male	Mates with	181-1437	2	Female	Or	181-1444	2	Female
181-1442	3	Male	"	181-1438	3	Female	"	181-1445	3	Female
181-1443	4	Male	n n	181-1439	4	Female	=	181-1446	4	Female
No s	ealing cap avail	able		Use Sealing Cap No: 207-0652	8			Use Sealing Cap No: 207-0652		

Connector Set (Cable-Mount Plug & In-Line Socket)							
RS Stock No: No. of Contacts							
181-1447	3	Equivalent to 181-1442 Plug + 181-1438 Socket (Without Crimps)					

	Crimp Terminals							
Г	Pack of 20	Pack of 100						
Г	181-1466	181-1448	5A AWG 24-20 Male (for 4-Pole Shells Only)					
	181-1467	181-1449	5A AWG 24-20 Female (for 4-Pole Shells Only)					
	Pack of 10	Pack of 100						
	181-1468	181-1450	10A AWG 26-22 Male (for 2 & 3-Pole Shells)					
	181-1469	181-1451	10A AWG 26-22 Female (for 2 & 3-Pole Shells)					
Г	181-1470	181-1452	10A AWG 18 Male (for 2 & 3-Pole Shells)					
	181-1473	181-1455	10A AWG 16 Female (for 2 & 3-Pole Shells)					

	Crimp Removal Tools							
ſ	181-1459 For 5A Crimps (4-Pole Shells Only)							
	181-1460	For 10A Crimps (2-Pole and 3-Pole Shells)						