

## Features

- Made of polypropylene (PP) for enhanced chemical resistance.
- Designed for securing cables in chemical industry environments.
- Halogen-free and RoHS compliant.

## RS PRO Cable Ties

RS Stock No.: 0656087



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

This cable tie is made from durable polypropylene (PP), offering excellent chemical resistance for use in demanding environments. Designed for secure bundling, it is ideal for applications in the chemical industry. Available in black and natural colours, it is halogen-free and fully RoHS compliant, ensuring safety and environmental responsibility.

## General Specifications

|                               |                                                    |
|-------------------------------|----------------------------------------------------|
| Series                        | Polypropylene                                      |
| Type                          | Non-Releasable                                     |
| Colour                        | Black                                              |
| Material                      | PP                                                 |
| Finish                        | Smooth                                             |
| Application                   | Designed for quick installation and cable bundling |
| Resistant To                  | Not specified                                      |
| UV Resistant                  | No                                                 |
| Minimum Operating Temperature | Not specified                                      |
| Maximum Operating Temperature | Not specified                                      |
| Fire Behaviour                | Self-Extinguishing                                 |
| Quantity                      | 100                                                |

## Mechanical Specifications

|                  |       |
|------------------|-------|
| Length           | 240mm |
| Width            | 7.6mm |
| Tensile Strength | 294N  |

## Approvals

|              |       |
|--------------|-------|
| Declarations | REACH |
|--------------|-------|

---

|               |                                         |
|---------------|-----------------------------------------|
| Standards Met | Chemical Resistance, Halogen-Free, RoHS |
|---------------|-----------------------------------------|