



Part Number : [2196812215](#)
Product Description : Pre-Crimped Lead SL
Female-to-Pigtail, Gold (Au) Plating,
450.00mm Length, 26 AWG, Red
Series Number : 219681
Status : Active
Product Category : Power and Signal Cable
Assemblies




Documents & Resources

Drawings
[2196812215_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2024)6225-DC (07 Nov 2024) |
| EU RoHS | Compliant per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|------------------------|--|
| Status | Active |
| Category | Power and Signal Cable Assemblies |
| Series | 219681 |
| Description | Pre-Crimped Lead SL Female-to-Pigtail, Gold (Au) Plating, 450.00mm Length, 26 AWG, Red |
| Application | Signal, Wire-to-Board, Wire-to-Wire |
| Assembly Configuration | Pre-crimped Lead Only |
| Connector to Connector | SL-to-Pigtail |
| Product Name | SL |
| UPC | 195842872400 |

Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 450.00mm |
| Circuits (Loaded) | 1 |
| Circuits (maximum) | 1 |
| Color - Resin | Red |
| Gender | Female-Pigtail |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Net Weight | 1.094/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Plating min - Mating | 0.380µm |
| Plating min - Termination | 2.000µm |
| Single Ended | Yes |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type | UL 11028 |
| Wire Insulation Diameter | 1.52mm max. |
| Wire Size (AWG) | 26 |

Use with Part(s)

| Description | Part Number |
|---|--------------|
| SL Single Row Crimp Housings and CPA Retainers | <u>70066</u> |
| SL Dual Row Crimp Housings | <u>70450</u> |

This document was generated on Jan 17, 2025