


Visuels :



1889 ARDENT



Descriptif :

FR Pantalon stretch léger et résistant - zéro métal

Bouton plastique 4 trous Ø 20mm - Braguette zip injecté plastique - Ceinture composée de 5 passants larges - Ceinture élastiquée côtés - 5 poches : Poches italiennes - Poche cuisse gauche à pli plat, fermée par rabat et scratch - Poche dos droite plaquée - Poche mètre - Attache porte marteau - Points d'arrêt rouges - Transfert sur poche cuisse - Ourlet magique (+5 cm)

Composition :

- Ripstop 65% polyester 33% coton 2% élasthanne - 200 g/m²

Tailles : 36 à 54 - Coloris : Gris charcoal

Longueur entrejambe : 78 cm

EN Lightweight and resistant stretch pants - metal free

Plastic button 4 holes Ø 20mm - Vislon zippered fly - Belt with 5 wide loops - Elasticated sides - 5 pockets: Italian pockets - Left thigh pocket with round pleat, closed with flap + magic tape - Patched pocket on back right side - Ruler pocket - Hammer carrier - Red bartacks - Transfer on thigh pocket - Magic hem (+2 inches)

Composition:

- Ripstop 92% polyamide 8% elastane - 260 g/m²

UK/US sizes: 28 to 43 - Colours: Charcoal grey
Inside leg: 31 inches