

FEATURES

- Available in 13 sizes
- Ergonomic soft-grip handles & premium-quality plastics for a comfortable grip
- Phosphate coated tip for increased friction on fixings, reducing the risk of rounding or damaging the screws

RS PRO Flat Standard Screwdriver (Flared Tip)

RS Stock No.: 1829669



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Introducing flared tip slotted screwdrivers from our trusted and reliable own brand RS PRO, a range of durable screwdrivers suitable for use with slotted screws and terminals. The screwdrivers feature a chrome vanadium molybdenum steel blade with a matt chrome finish, providing long life and corrosion resistance properties. These durable screwdrivers also feature an ergonomic soft grip handle for enhanced comfort and grip, assisting with torque.

RS Pro also provides a range of screwdrivers with smaller tip sizes, featuring a cabinet tip for optimal use when reaching into confined spaces where screws are recessed.

Features and benefits

- Made with durable Chrome Vanadium Molybdenum steel providing excellent durability
- Matte chrome finish for excellent corrosion resistance
- Black tip for distinct contrast between screw and tip
- Soft grip handle for enhanced grip and control
- Ideal for use with terminals
- Available in a variety of sizes

Common applications

Slotted screwdrivers with flared tips are an essential hand tool in many tool kits, used in a wide range of applications such as:

- Construction
- DIY
- Industrial
- Electrical
- Automotive

General Specifications

Screwdriver Type	Slotted Head; Ergonomic; Standard; Rounded Blade
Number of Pieces	1
Tip Type	Straight; Slotted; Flat; Flared Tip

Electrical Specifications

ESD Safe	No
-----------------	----

Mechanical Specifications

Tip Size	5.5 mm; 6.5 mm; 8 mm; 10 mm; 12 mm
Blade Length	100 mm; 125 mm; 150 mm; 175 mm; 200 mm; 250 mm
Overall Length	200 mm; 210 mm; 225 mm; 235 mm; 250 mm; 260 mm; 270 mm; 295 mm; 300 mm; 310 mm; 320 mm; 370 mm
Blade Material	Chrome Vanadium Molybdenum Steel
Handle Material	Rubberised Soft Grip; PPE; TPE
Blade Shape	Round
Blade Finish	Black Phosphate; Black Tip; Chrome

Available sizes in range

Stock No.	Product Name	Tip Size (mm)	Blade Length (mm)	Overall Length (mm)
1829666	Slotted Screwdriver (Flared Tip)	5.5	100	200
1829667	Slotted Screwdriver (Flared Tip)	5.5	125	225
1829668	Slotted Screwdriver (Flared Tip)	5.5	150	250
1829669	Slotted Screwdriver (Flared Tip)	5.5	200	300
1829670	Slotted Screwdriver (Flared Tip)	6.5	100	210
1829671	Slotted Screwdriver (Flared Tip)	6.5	125	235
1829673	Slotted Screwdriver (Flared Tip)	6.5	150	260
1829674	Slotted Screwdriver (Flared Tip)	6.5	200	310
1829675	Slotted Screwdriver (Flared Tip)	8	150	270
1829676	Slotted Screwdriver (Flared Tip)	8	175	295
1829677	Slotted Screwdriver (Flared Tip)	10	200	320
2539672	Slotted Screwdriver (Flared Tip)	10	250	370
1829678	Slotted Screwdriver (Flared Tip)	12	250	370

Approvals

IEC Name	DIN ISO 2380-1
-----------------	----------------

Similar Products

Parameters	1829682
Brand	RS PRO
Screwdriver Type	Hex Bolster
Number of Pieces	1
Tip Type	Slotted
ESD Safe	No
Tip Size	10mm
Blade Length	175mm
Blade Material	Chrome Vanadium Molybdenum
Overall Length	220mm
Handle Material	PPE/TPE
Blade Finish	Chrome
Special Features	Hex Bolster
Blade Shape	Flared
IEC Name	DIN ISO 2380-1





