

## FEATURES

- **Sintered Bronze Material:** Provides high wear resistance and durability
- **Flanged Design:** Ensures secure and precise positioning
- **Dynamic Load Rating of 14 N/mm<sup>2</sup>:** Suitable for applications with moderate dynamic loads
- **Static Load Rating of 50 N/mm<sup>2</sup>:** Capable of handling high static loads
- **ISO 9001:2008 Certified:** Meets international quality management standards

## RS PRO 1.37 in Flanged Plain Bearing, Sintered Bronze

RS Stock No: 518-175



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

## Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, it offers excellent durability and performance in various industrial settings. The flanged design ensures secure positioning, making it ideal for use in machinery where precise alignment is crucial.

## General Specifications

Bore Size	1.37 in
Dynamic Load Rating	14 N/mm <sup>2</sup>
Product Type	Plain Bearing
Static Load Rating	50 N/mm <sup>2</sup>
Sub Type	Flanged

## Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	1.62 in
Width	1-1/4 in

## Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

