



ENGLISH

Datasheet

Stock No: 259-6424

RS Pro Green Round Polyurethane Belt



Product Details

Round Section Polyurethane

Non-reinforced round polyurethane belting in a range of diameters and material specifications. Easily joined on site these belts require no special safety measures or complicated joining procedures.

Fast jointing

Oil/chemical/abrasion resistant

High load capacity

High tensile strength

Easily cleaned

Note

Working load quoted is based on 8% tension.



ENGLISH

Specifications:

Colour	Green
Diameter	4mm
Minimum Pulley Diameter	38mm
Length	30m
Working Load	3.4kg
Hardness	88Type A
Food Certified	No
Minimum Operating Temperature	-30°C
Maximum Operating Temperature	+80°C