


Marker for terminal blocks - UC1-TMF 5 OG - 0828206

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Marker for terminal blocks, Sheet, orange, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into flat marker groove, Lettering field: 4.45 x 5.2 mm




Why buy this product

- The UC1-TMF ... UniCard labeling range includes markers for Weidmüller, Wago, ABB (entrelec), Conta-Clip, and Klemsan terminal blocks
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- The multi-section marking strips are easy to fit and can be easily separated if required
- The markers support multi-line labeling
- The sheets provide space for including function texts



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 046356 480574 |
| Weight per Piece (excluding packing) | 7.88 g |
| Custom tariff number | 39269097 |
| Country of origin | Poland |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|-----------|------|
| Width (a) | 5 mm |
|-----------|------|

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

General

| | |
|---|--------------------------------|
| Color | orange |
| Components | free from silicone and halogen |
| Inflammability class according to UL 94 | V2 |

Marker for terminal blocks - UC1-TMF 5 OG - 0828206

Technical data

General

| | |
|-------------------------------------|------------------------------|
| Material | PA |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 96 |
| Number of individual labels per row | 12 |
| Marking mounting type | Snap into flat marker groove |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |

Accessories

Accessories

Magazine

Magazine - P1 UC-MAG 4 - 5146105



Magazine, for CMS-P1-PLOTTER, for accommodating UC-TMF..., UC1-TMF..., UC-WMT...

