

PRODUCT-DETAILS

TC347

2/4WAY MTG BASE 1.1X1.1IN NAT



General Information

Extended Product Type	TC347
Product ID	7TAG009820R0050
EAN	5414363058601
Catalog Description	2/4WAY MTG BASE 1.1X1.1IN NAT
Long Description	Four-Way and Two-Way Mounting Base With Open Leg Design, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 8.5mm (0.33 Inches), Screw Mounting Method or Two-Component Glue, #8 Screw, Mounting Hole Size of 4.4mm (0.17 Inches), Bulk Pack

Ordering

EAN	5414363058601
UPC	786210889528

Container Information

Package Level 1 Units	1000 piece
Package Level 2 Units	5000 piece
Package Level 2 Width	13.4 in 340 mm
Package Level 2 Height	9.5 in 241 mm
Package Level 2 Depth / Length	21 in 533 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19770309
Material	Nylon/Polyamide 6.6
Mounting Type	Epoxy Glue (TC2PA)/Screw
Number of Batteries	0
Process Temperature Rating	-40 to +185 °F
Product Name	TY-RAP FASTENING
Product Type	Mounting Base
Special Functions	Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC347
Instructions and Manuals	TC347
REACH Declaration	9AKK107992A8789
RoHS Information	9AKK107991A8363

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

