

Circular Saw XGT®

RS001G

40V max • 6 400 min⁻¹ • 185 mm

Highly robust circular saw for demanding applications.

40V max XGT® Li-ion battery and brushless motor makes this saw excellent choice for demanding applications. The blade can reach up to 6 400 min⁻¹ to ensure high cutting performance with large cutting capacity.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	6400 min ⁻¹
Max. Cutting Depth at 90°	65 mm
Max. Cutting Depth at 45°	45 mm
Max. Bevel Range (Left)	0 - 53 °
Sound Power Level (L _{WA})	103 dB(A)
Sound Pressure Level (L _{pA})	95 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Product Dimensions (L x W x H):	446 x 196 x 270 mm
Tool weight with battery	5,0 - 6,2 kg
Max. Cutting Depth at 53°	38 mm
Blade Diameter	185 mm
Bore Size (Arbor Diameter)	30 mm

User benefits

- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Brushless maintenance-free and long-life motor
- Battery protection system automatically shuts off power when the battery level is low
- Retractable, extra-wide tool hook secures the tool when not in use

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing