




Switches > Tactile Switches



Contact Current Rating: 50 mA
Actuator Style: Round Actuator
Operating Function: NO
Contact Base Material: Copper Alloy
Switch Contact Plating Material: Silver

Features

Product Type Features

Leg Style	Gull Wing
Switch Connection Type	Printed Circuit Board
Illuminated	With
Actuator Style	Round Actuator

Configuration Features

Switch Feedback Type	Tactile
ESD Grounding Terminal	Without
Ganged	With
Operating Function	NO
Support Bracket	Without
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single

Electrical Characteristics

Operating Voltage	24 VDC
-------------------	--------



Body Features

Case Material	Polyamide
Actuator Profile	Extended
Case Color	Brown
Actuator Material	PPS
Cover Material	Steel
Actuator Force	100 g[3.52 oz]
Product Orientation	Vertical
Actuator Color	Brown

Contact Features

Contact Current Rating	50 mA
Contact Base Material	Copper Alloy
Switch Contact Plating Material	Silver

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Low Profile	With
Process Sealed	No

Dimensions

	.138 in
Product Height	4.3 mm[.169 in]
Actuator Length	.7 mm[.028 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C
-----------------------------	-------------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1825910-6
FSM4JH=6MM TACT SWITCH, HIGH TEMP



TE Part # 2-1977223-8
FSM14JSMAS=6MM TACT SWITCH, SMT 160gf



TE Part # 2-1825910-7
FSM14JH=6MM TACT SWITCH, HIGH TEMP



TE Part # 3-1437565-0
FSM2JSMATR=ON T/R



TE Part # 4-1437565-2
FSM4JSMATR=TACT SWITCH 6X6MIL

Also in the Series | [Alcoswitch FSMJSMA](#)



Tactile Switches(22)

Customers Also Bought



TE Part #1-1423364-2
W57-XB1A4A10-5=CKTBKR,THERM,
PB,QC.250,BU




TE Part #1SNG607015R0000
EP-LN-M32-BL-A




TE Part #2-1879207-1
RN 0603 324K 0.1% 10PPM 5K RL



TE Part #2176272-7
RU 0805 3K32 0.01% 2PPM 1K RL



TE Part #6-2176422-4
TLRP 2512 3.0W R039 1% 50PPM 4K RL



TE Part #5-147278-7
08 MTE HDR SRRA SFMNT .100CL




TE Part #5-1437653-1
6PCV-12-006=6PCV ASSEMBLY



TE Part #9-1462037-9
IM06CGR=IM RELAY 140mW12V HDV



TE Part #254835-E
STVC 96 M ABC VVV 4-00 EE * * 247
E007 1



TE Part #7-1768829-1
LBC-RAS-10408-1

Documents

Product Drawings

FSM2JSMLTR=TACT SWITCH,SMT,T&R

English

CAD Files

Customer View Model

ENG_CVM_CVM_1571527-2_V1.3d_stp.zip

English



3D

Customer View Model

[ENG_CVM_CVM_1571527-2_V1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1571527-2_V1.3d_igs.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Products for Mobile Equipment](#)

English