

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability.
- **1.25 in Inside and Outside Diameter:** Ensures compatibility with a wide range of shafts and housings.
- **0.13 in Thickness:** Offers a compact solution for tight spaces.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads effectively.

RS PRO Sintered Bronze Thrust Washer, 1.25 in Diameter

RS Stock No: 528-888



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO thrust washer is designed for applications requiring reliable axial load support. Made from high-quality sintered bronze, it offers excellent durability and performance in various industrial settings. Its compact design and robust material make it ideal for reducing friction and wear between moving parts.

General Specifications

Dynamic Load Rating	14 N/mm ²
Product Type	Thrust Washer
Static Load Rating	50 N/mm ²
Sub Type	Washer

Mechanical Specifications

Inside Diameter	1.25 in
Material	Sintered Bronze
Outside Diameter	1.25 in
Thickness	0.13 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------