

Pendant control

46-447.1818

Distribution by
Rs-online



<https://rs-online.eao.com/component/46-447.18...>

Your product:



46-447.1818 Pendant control

FRONT

Colour: Grey

MOUNTING

Mounting cut-out: Ø 22 mm

Mounting type: Panel mounting

ELECTRICAL CHARACTERISTICS

Rated insulation voltage Ui: Ui 300V - Uimp 2.5KV (IEC-EN60947-1)

Pollution degree: 3

Protection class: II, according to EN / IEC 61140

MECHANICAL CHARACTERISTICS

Tightening torque: 0.8 ... 1.2 Nm (7.1÷10.6 Lb-in)

Weight: 0.2 kg

AMBIENT CONDITION

IP front protection: IP65, IP66

IK front protection: IK08

Operating temperature: – 35 °C ... + 80 °C

CERTIFICATE

Approbations: CSA, UL

