



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 10:49 (UTC)



24024CAME4

Spherical Roller Bearings

Parts Number

24024CAME4C4

Boundary Dimensions

d	120	mm	Bore diameter
D	180	mm	Outside diameter
B	60	mm	Width
r (min.)	2	mm	Chamfer dimension

Basic Load Ratings

Cr	480000	N	Basic dynamic load rating
C0r	680000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	2600	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	3600	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	1500	min-1	Grease lubrication
Oil (Oil-bath)	2000	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	130	mm	Diameter of shaft abutment
Da (min.)	158	mm	Diameter of housing abutment
Da (max.)	170	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Calculation factors

e	0.32	Constant
Y2	3.2	Axial load Factors
Y3	2.1	Axial load Factors
Y0	2.1	Axial load Factors

Mass

Mass approx.	5.33	kg	Mass approx.
--------------	------	----	--------------

