

# Drawn cup needle roller bearings with closed end BK2020 (Series BK)

to DIN 618/ISO 3245

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

Fw	20 mm	
D	26 mm	
C	20 mm	Tolerance: 0/-0,3
Ct min	17,3 mm	
rmin	0,8 mm	
m	27 g	Mass
Cr	15700 N	Basic dynamic load rating, radial
C0r	26000 N	Basic static load rating, radial
Cur	3600 N	Fatigue limit load, radial
ng	12700 1/min	Limiting speed

n <sub>9r</sub>	9300 1/min	Reference speed
	IR17X20X20-XL	Suitable inner ring
	LR17X20X20,5	Suitable inner ring
	SD20X26X4	Suitable sealing ring
	G20X26X4	Suitable sealing ring

