



## **DATA SHEET: T5 EM BATTEN SERIES**

230V T5 Emergency Batten



RS Stock No.: 851-3012 851-3024 851-3030 851-3034 851-3040 851-3015 T5128EM T5135EM T5149EM T5228EM T5235EM T5249EM MLA part code: Description: IP20 T5 Batten EM Series White Finishes: 2.225 2.5 Weight (kg): 2.5 2.65 2.8 2.8 Wattage (W): 2 x 35 2 x 49 28 35 49 2 x 28 Total circuit Power (W): 31 38 44 62 75 106 1175 (I) 1475 (l) 1475 (l) 1475 (l) 1475 (l) 1475 (I) Overall length (mm): 230V 50Hz Input voltage: Lamp Type: Pressed Steel with Polycarbonate end caps Construction: Control gear: High Frequency soft start ballast Class I Class: IP20 IP rating: 1 Year Warranty: Photometric data: Nο Dimmable: Νo Instruction sheet: Yes Origin of Manufacture: China ISO 9001 Quality assurance system: Declaration of Conformity (held on file): Yes Manufactured & accordance with: EN60598

