2529 : Viper® i26+ Manual Hydraulic Press-Fitting Machine























The + product :

Multi-material press-fitting, **up to Ø 26 mm** in multiple layers.

Ergonomic and space-saving

Sound indicator at end of crimping.

Description

Manual hydraulic press-fitting machine for use with insert sets.

Easy feed thanks to a new, optimized, high-performance staged piston hydraulic device with extended service life.
Crimping end indicator: sound signal when reaching maximum pressure.
Minimized weight (only 2.5 Kg): one-handed use thanks to its ergonomic design, slim format and compact head for access to confined spaces.
Head swivels at 180° for easy use in all situations; Fast head opening / closing.
High quality steel hydraulic dispenser, jaw in anticorrosion treated hardened steel.
Machine protected by overpressure valve.
Non-slip Soft Touch® handle for perfect control.

Size: 366 x 63 x 88mm.
Supplied in a case VIRABOX

Wide choice of inserts: Virax has inserts for the majority of crimping systems available on the market.
Find compatibility between VIRAX fitting systems and inserts/clips using the Vir-app application or at the end of the catalogue.

More Information

Capacity	Copper: Ø 12 / 14 / 16 mm. PER, PEX: Ø 12 – 25 mm. Multilayer: Ø 12 - 26 mm. Except inserts HA26 and V15.

References

Sku	Description	Dimensions	Crimping force kN	kg
252910	Viper® i26+ Supplied in a case (without accessories)	390 x 190 x 120	42	3,540
252912	Viper® i26+ inserts RF-P 12 / RF-P 16 / RF-P 20	390 x 190 x 120	42	4,120
252913	Viper® i26+ inserts TH 16 / TH 20 / TH 26	390 x 190 x 120	42	4,250
252922	Viper® i26+ inserts U 16 / U 20 / U 25	390 x 190 x 120	42	4,250